



WNA006B



cubyko 2W SW +label holder compos. white

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting
Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Identification

Assembly arrangement Control element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 55 x 55 mm
Built-in depth 12 mm
Built-in depth flush-mounted boxes 40 mm
Height of P-touch band for labelling field 12 mm

Safety

Ingress Protection (IP) class IP55
Impact resistance IK IK08

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Connection

Type of contacts 2-way
Connector/plug type Turn screw lock

Texts

Installation mode For screw fastening
Type of connection With N-terminal
With plug-in terminals
Lighting Without lighting (cannot be illuminated)
Switch mode 2-way

Sustainability

REACH-SVHC free Yes