



JK1B066F2WA316

#### Technical Features

##### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

##### Electric current

|                                   |      |
|-----------------------------------|------|
| Breaking and opening capacity ldm | 0 kA |
|-----------------------------------|------|

##### Equipment

|                    |    |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

|                      |           |
|----------------------|-----------|
| Equipped with switch | No switch |
|----------------------|-----------|

|                    |   |
|--------------------|---|
| Number of switches | 0 |
|--------------------|---|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

##### Dimensions

|        |        |
|--------|--------|
| Height | 800 mm |
|--------|--------|

|       |        |
|-------|--------|
| Width | 470 mm |
|-------|--------|

|       |      |
|-------|------|
| Depth | 5 mm |
|-------|------|

##### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

##### Materials

|          |       |
|----------|-------|
| Material | Steel |
|----------|-------|

|          |      |
|----------|------|
| RAL code | 9002 |
|----------|------|

|        |            |
|--------|------------|
| Colour | Grey white |
|--------|------------|

##### Safety

|                  |                   |
|------------------|-------------------|
| Protection class | Isolation class I |
|------------------|-------------------|

|                      |      |
|----------------------|------|
| Impact resistance IK | IK05 |
|----------------------|------|

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP41 |
|-------------------------------|------|

|              |                              |
|--------------|------------------------------|
| Locking type | Special tool<br>Without lock |
|--------------|------------------------------|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|