



9626205

## Integro Insert-British Standard Socket Outlet with Earth Contact, Black Matt

### Technical Features

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	Black
RAL code	9005 9011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	55.50 mm
Width	55.50 mm
Built-in depth flush-mounted boxes	20 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Built in installation Screw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	1
-------------------	---

#### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

**Suitable for**

---

integro

---