



WGDCH3

3G multi-gang frame

Technical Features

Capacity

| | |
|-------------------|---|
| Number of gangs | 4 |
| Number of modules | 0 |

Materials

| | |
|--|--------------------|
| Colour | White |
| Surface finish | Glossy |
| Material | Polycarbonate (PC) |
| Contains recycled material (% of total plastic weight) | 0 % |
| Treatment | Untreated |

Dimensions

| | |
|----------------------------|-------|
| Height | 8 mm |
| Width | 86 mm |
| Depth | 8 mm |
| Number of units horizontal | 4 |
| Number of units vertical | 4 |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Mounting plate |
|-------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK02 |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |