



47893505



SCHUKO soc.out.hinged cover surf.-mtd,identical lockings,enhncd contact prot.,W1

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	76 mm
Width	76 mm
Depth	65 mm
Built-in depth flush-mounted boxes	0 mm
Height of P-touch band for labelling field	12 mm

Connection

Conductor cross-section	1.0 - 2.5 mm ²
-------------------------	---------------------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	Yes

Accessories

Has labelling field	Yes
---------------------	-----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor

Sustainability

Halogen free	Yes
RoHS conform	Yes