



WXF160V

**Schuko socket gallery 2P+E green**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Green
RAL code	6024
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

**Dimensions**

Height	45 mm
Width	45 mm
Number of units	1
Built-in depth flush-mounted boxes	40 mm

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	6
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Complete housing
Protection	Enhanced contact protection

**Suitable for**

gallery	
---------	--

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes