



WXF160N

Schuko socket gallery 2P+E night

Technical Features

Electric current

Rated current 16 A

Voltage

Output voltage 5 - 5 V

Use conditions

Operating temperature -10 - 35 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Jet black
RAL code 9005
Surface finish Satin finish
Material Polycarbonate (PC)
Treatment Varnished

Dimensions

Height 45 mm
Width 45 mm
Number of units 1
Built-in depth flush-mounted boxes 40 mm

Connectivity

Mounting type Click mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 6

Safety

With enhanced contact protection Yes
Impact resistance IK IK05
Ingress Protection (IP) class IP21

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover Complete housing
Protection Enhanced contact protection

Suitable for

gallery

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes