



WXF160D

**Schuko socket gallery 2P+E dune**

**Technical Features**

**Electric current**

Rated current 16 A

**Voltage**

Output voltage 5 - 5 V

**Use conditions**

Operating temperature -10 - 35 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour White  
RAL code 1013  
Surface finish Glossy  
Material Polycarbonate (PC)  
Treatment Untreated

**Dimensions**

Height 45 mm  
Width 45 mm  
Number of units 1  
Built-in depth flush-mounted boxes 40 mm

**Connectivity**

Mounting type Click mounting

**Equipment**

Connector/plug type socket outlet SCHUKO  
Rotated central insert No  
With hinged lid No  
With round protective earth pin No  
With signal lamp No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 6

**Safety**

With enhanced contact protection Yes  
Impact resistance IK IK05  
Ingress Protection (IP) class IP21

**Functions**

With orientation lighting No  
With function lighting No

**Identification**

With imprint No

**Texts**

Cover Complete housing  
Protection Enhanced contact protection

**Suitable for**

gallery

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes