



CCA216U

RCCB 2P 16A 10mA A Class

Technical Features

Architecture

Type of pole	1P+N
Number of poles	2

Electric current

Rated current	16 A
Rated residual operating current I_{dn}	10 mA
Breaking and opening capacity I_{dm}	1.50 kA
Rated conditional short-circuit current I_{nc} according to EN61008-1	6 kA
Rated current -25°C	16 A
Rated current at -20°C	16 A
Rated current -15°C	16 A
Rated current -10°C	16 A
Rated current -5°C	16 A
Rated current at 0°C	16 A
Rated current 5°C	16 A
Rated current 10°C	16 A
Rated current 15°C	16 A
Rated current at 20°C	16 A
Rated current 25°C	16 A
Rated current 30°C	16 A
Rated current 35°C	16 A
Rated current at 40°C	16 A
Rated current at 45°C	16 A
Rated current at 50°C	16 A
Rated current 55°C	16 A
Rated current 60°C	16 A
Rated current 65°C	16 A
Rated current 70°C	16 A

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage U_e	230 - 230 V
Type voltage supply	AC
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V
Max. operating voltage	253 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Capacity

Number of modules	2
-------------------	---

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect
Nominal tightening torque	2.80 - 2.80 Nm

Connection

Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section flexible conductor	16 mm ²
Cross-section rigid conductor	25 mm ²

Power

Total power loss under IN	2.40 W
---------------------------	--------

Use conditions

Max. Altitude	2000 m
---------------	--------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

Dimensions

Height	83 mm
Width	35 mm
Depth	70 mm

Sustainability

RoHS conform	Yes
--------------	-----