



WXF165B

**Schuko socket gallery with lid 2P+E pure-white**

**Technical Features**

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | Traffic white      |
| RAL code       | 9016               |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Height                             | 40 mm |
| Width                              | 45 mm |
| Number of units                    | 1     |
| Built-in depth flush-mounted boxes | 40 mm |

**Installation, mounting**

|                               |                        |
|-------------------------------|------------------------|
| Mounting-/Connection Position | Horizontal<br>Vertical |
|-------------------------------|------------------------|

**Connectivity**

|               |   |
|---------------|---|
| Mounting type | Claw mounting<br>Screw connection<br>Screw mounting |
|---------------|---|

**Equipment**

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert            | No     |
| With hinged lid                   | Yes    |
| With round protective earth pin   | No     |
| With signal lamp                  | No     |

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Cover, door**

|             |                           |
|-------------|---------------------------|
| Type of lid | Self-closing hinged cover |
|-------------|---------------------------|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

**Safety**

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | Yes  |
| Impact resistance IK             | IK05 |
| Ingress Protection (IP) class    | IP21 |

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

---

**Texts**

|            |                             |
|------------|-----------------------------|
| Cover      | Complete housing            |
| Protection | Enhanced contact protection |

---

**Suitable for**

gallery

---

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |