



WXF165T

**Schuko socket gallery with lid 2P+E titane**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Titanium
RAL code	9006
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

**Dimensions**

Height	40 mm
Width	45 mm
Depth	43.35 mm
Number of units	1
Built-in depth flush-mounted boxes	40 mm

**Installation, mounting**

Mounting-/Connection Position	Horizontal Vertical
-------------------------------	------------------------

**Connectivity**

Mounting type	Click mounting Screw mounting
---------------	----------------------------------

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Self-closing hinged cover
-------------	---------------------------

**Capacity**

Number of modules	6
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

---

**Texts**

Cover	Complete housing
Protection	Enhanced contact protection

---

**Suitable for**

gallery

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes