



WXF165N

Schuko socket gallery with lid 2P+E night

Technical Features

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

Dimensions

Height	40 mm
Width	45 mm
Number of units	1
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting-/Connection Position	Horizontal Vertical
-------------------------------	------------------------

Connectivity

Mounting type	Claw mounting Screw connection Screw mounting
---------------	---

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Self-closing hinged cover
-------------	---------------------------

Capacity

Number of modules	6
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Enhanced contact protection

Suitable for

gallery

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes