



VU24ET

Encl.,Volta,flush,2x12MOD,IP30,Version Spain,transparent door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Flush mounting
-------------	----------------

Electric current

Rated current	63 A
---------------	------

Power

Maximum power loss per cabinet at $\Delta T=20K$	17.50 W
--	---------

Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	24
-------------------	----

Number of half modules terminals per rail	48
---	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	505.50 mm
--------	-----------

Width	348 mm
-------	--------

Depth	94.50 mm
-------	----------

Built-in height	490 mm
-----------------	--------

Built-in width	335 mm
----------------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	90 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Product Datasheet

VU24ET

Materials

Ultraviolet-resistant

Yes

Safety

Protection class

Isolation class II

Ingress Protection (IP) class

IP30

Locking type

Snap on lock
Without lock

Glow wire test

650 °C

Sustainability

RoHS conform

Yes