



JK1E32F

**125A TPN Extension box, invicta, 32 Module with Din Rail, depth120mm, flush**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

**Equipment**

Number of rows	2
Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	No chassis

**Capacity**

Number of modules	10
-------------------	----

**Dimensions**

Height	450 mm
Width	430 mm
Depth	5 mm
Number of width units	16

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	No

**Materials**

Material	Steel
RAL code	9002
Colour	Grey white

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP41
Locking type	Special tool Without lock

**Architecture**

Number of poles	32
-----------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes