



BRAP651001ELN

Alu-trunking base 65x100, anodised

Technical Features

Dimensions

Height	65 mm
Width	100 mm
Length	2000 mm

Cover, door

Number of mountable lids	1
Cover width 1	80 mm
Cover width 2	0 mm
Cover width 3	0 mm

Dimensions

Inner cross-section	5400 - 5400 mm ²
---------------------	-----------------------------

Capacity

Max. number of cables (Ø11 mm, 50% filled, with devices)	10
Max. number of cables (Ø11mm, 50% filled, without devices)	28

Compatibility

Device installation compatible format	Standard 60 mm, CEE, Ecoline, EIB
---------------------------------------	-----------------------------------

Installation, mounting

Base perforation	No
------------------	----

Materials

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP40

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Coupling pins as separate reference
-------------------	-------------------------------------

Equipment

Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	Yes

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

