



382610



Change-over switch 2pole for lock cylinders, light control

Technical Features

Electric current

Switching current 16 AX (100W LED (SBL))

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Materials

Surface finish Matt

Material Metal
Plastic

Treatment Untreated

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 70.80 x 70.80 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Key

Electric current

Rated current 16 A

Texts

Installation mode For screw fastening
Without spreader claws

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole off/change-over

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes