



WGDS115SNB

## 15A SINGLE SWITCHED SOCKET, Noble Bronze

### Technical Features

#### Electric current

|                |      |
|----------------|------|
| Rated current  | 15 A |
| Output current | 0 mA |

#### Voltage

|                 |           |
|-----------------|-----------|
| Rated voltage   | 250 V     |
| Nominal voltage | 220-250 V |
| Output voltage  | 0-0 V     |

#### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Power

|                           |     |
|---------------------------|-----|
| Output power              | 0 W |
| Power consumption standby | 0 W |

#### Materials

|                                                        |                    |
|--------------------------------------------------------|--------------------|
| Colour                                                 | Bronze             |
| Surface finish                                         | Matt               |
| Material                                               | Polycarbonate (PC) |
| Treatment                                              | Coated             |
| Contains recycled material (% of total plastic weight) | 0 %                |

#### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 30 mm |
| Width                              | 86 mm |
| Depth                              | 22 mm |
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 22 mm |

#### Connection

|                                                          |                          |
|----------------------------------------------------------|--------------------------|
| Connector/plug type                                      | British Standard         |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |

#### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Back           |

#### Connectivity

|                         |                  |
|-------------------------|------------------|
| Type of connection      | Screw terminal   |
| With claw mounting      | No               |
| Mounting type           | Screw mounting   |
| Connector/plug type USB | British Standard |

#### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |
| With lock                         | No               |

#### Accessories

|                     |      |
|---------------------|------|
| Has labelling field | No   |
| Pre-equipped with   | None |

---

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

---

**Safety**

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | No   |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |

---

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

---

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

---

**Suitable for**

|       |  |
|-------|--|
| shark |  |
|-------|--|

---

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |