



WXPPS12B

IP66 10AX 1 Gang Press Bell Switch

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Number of poles	2
-----------------	---

Materials

Colour	Light grey
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No

Dimensions

Height	90 mm
Width	90 mm
Depth	50 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes