



HIB463M

Motorized transfer switch 4P 800A

Technical Features

Voltage

Rated operational voltage U _e	380 - 415 V
--	-------------

Electric current

Rated current	800 A
---------------	-------

Rated conditional short-circuit current I _{cc} with gl-gG fuses	50 kA
--	-------

Power

Rated operational power under 400 V AC AC1	526000 W
--	----------

Architecture

Number of poles	4
-----------------	---

Device construction type	Fixed built-in
--------------------------	----------------

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Suitable for distribution board	Yes
---------------------------------	-----

Installation, mounting

Mounting on	Mounting plate
-------------	----------------