



HIC406R

**Automatic motorized changeover switch 4P 63A**

**Technical Features**

**Voltage**

Rated operational voltage $U_e$	380 - 415 V
Rated insulation voltage $U_i$	800 V
Rated impulse withstand voltage $U_{imp}$	6000 V

**Electric current**

Rated current	63 A
Rated short-time withstand current $I_{cw}$ IEC 60947	3.50 kA
Rated conditional short-circuit current $I_{cc}$ with gl-gG fuses	50 kA

**Power**

Rated operational power under 400 V AC AC1	41000 W
--	---------

**Architecture**

Number of poles	4
Type of pole	4P

**Controls and indicators**

Motor drive integrated	Yes
------------------------	-----

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP00
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------