



HIC410A

**Motorized changeover switch 4P 100A 400V**

**Technical Features**

**Voltage**

Rated operational voltage  $U_e$  380 - 415 V

**Electric current**

Rated current 100 A

Rated conditional short-circuit current  $I_{cc}$  with gl-gG fuses 50 kA

**Power**

Rated operational power under 400 V AC AC1 65000 W

**Architecture**

Number of poles 4

Device construction type Fixed built-in

**Compatibility**

Suitable for DIN Rail Yes

Suitable for distribution board Yes

**Installation, mounting**

Mounting on DIN rail  
Mounting plate

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes