



JK024

**24 Mod DIN Rail Box Plain**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	100 A
---------------	-------

**Equipment**

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	Yes
Has neutral terminal block	Yes

**Capacity**

Number of modules	24
-------------------	----

**Dimensions**

Height	472 mm
Width	326 mm
Depth	125 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Number of width units	24
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	Yes
-----------------------------	-----

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Barrel lock Key lock

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes