



HIC412R

Automatic motorized changeover switch 4P 125A

Technical Features

Voltage

Rated operational voltage U_e	380 - 415 V
Rated insulation voltage U_i	800 V
Rated impulse withstand voltage U_{imp}	6000 V

Electric current

Rated current	125 A
Rated short-time withstand current I_{cw} IEC 60947	3.50 kA
Rated conditional short-circuit current I_{cc} with gI-gG fuses	15 kA

Power

Rated operational power under 400 V AC AC1	82000 W
--	---------

Architecture

Number of poles	4
Type of pole	4P

Controls and indicators

Motor drive integrated	Yes
------------------------	-----

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------