



HIC425E

**ATS with energy management 4x 125A**

**Technical Features**

**Voltage**

Rated operational voltage U <sub>e</sub>	380 - 415 V
--	-------------

**Electric current**

Rated current	125 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	82000 W
--	---------

**Architecture**

Number of poles	4
Device construction type	Fixed built-in

**Compatibility**

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes