



JG440IN

**IP66 40A 3P SW NEUTRAL ISOLATOR**

**Technical Features**

**Architecture**

Number of poles	4
Type of pole	3P+N

**Electric current**

Rated current	40 A
Acceptable current rating AC21	40 A
Acceptable current rating AC21 category A	40 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	0.48 kA
Acceptable current rating AC22 category A	40 A

**Voltage**

Rated operational voltage U <sub>e</sub>	380 - 440 V
--	-------------

**Electric current**

Acceptable current rating AC23 category A	40 A
---	------

**Voltage**

Rated insulation voltage U <sub>i</sub>	440 V
---	-------

**Installation, mounting**

Nominal tightening torque	2.50 - 2.50 Nm
---------------------------	----------------

**Dimensions**

Height	170 mm
Width	84 mm
Depth	87 mm

**Safety**

Ingress Protection (IP) class	IP66
-------------------------------	------

**Power**

Rated operational power under 400 V AC AC23	19800 W
---	---------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	6 - 10 mm <sup>2</sup>
-------------------------------	------------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----