



BR264N

Earth leakage add-on block 2P 63A 500mA AC S Class

Technical Features

Voltage

Rated operational voltage U _e	230 - 400 V
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I _{dn}	500 mA
Rated current	63 A

Architecture

Number of poles	2
Neutral position	Right

Capacity

Number of modules	2
-------------------	---

Installation, mounting

Nominal tightening torque	2.90 - 2.90 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm