

Design 50,16Way,High Integrity,100A Switch,2\*100A 30mA RCCB

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Architecture**

Number of poles 2

**Functions**

Overvoltage protection Yes

**Installation, mounting**

Suitable for outdoor usage No

**Capacity**

Number of modules 16

**Electric current**

Rated current 100 A

**Dimensions**

Depth 105 mm

Height 284 mm

Width 539 mm

Thickness of sidewall 1 mm

**Cover, door**

Interlockable No

Door/cover is transparent No

**Materials**

RAL code 9010

Colour Pure white

Material Steel

**Connection**

Number of accessible phases 1

**Equipment**

Number of rows 1

Number of rails 1

Extension possible No

**Safety**

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC