

Product Datasheet

HIC425G



HIC425G

Automatic transfer switch 4x 250A

Technical Features

Voltage

Rated operational voltage Ue	380 - 415 V
------------------------------	-------------

Electric current

Rated current	250 A
Rated conditional short-circuit current Icc with gl-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	164000 W
--	----------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	No
Suitable for distribution board	Yes

Installation, mounting

Mounting on	Mounting plate
-------------	----------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes