

# Product Datasheet

## HIC425E



HIC425E

### ATS with energy management 4x 250A

#### Technical Features

##### Voltage

Rated operational voltage U <sub>e</sub>	380 - 415 V
--	-------------

##### Electric current

Rated current	250 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	50 kA

##### Power

Rated operational power under 400 V AC AC1	164000 W
--	----------

##### Architecture

Number of poles	4
Device construction type	Fixed built-in

##### Compatibility

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes