



JK044\_IMG

### 44 Mod DIN Rail Box Plain

#### Technical Features

##### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

##### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 2   |
| Number of rows             | 2   |
| Number of section in width | 1   |
| With lock                  | Yes |
| Has neutral terminal block | Yes |

##### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 44 |
|-------------------|----|

##### Dimensions

|        |        |
|--------|--------|
| Height | 472 mm |
| Width  | 505 mm |
| Depth  | 125 mm |

##### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

##### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 44 |
|-----------------------|----|

##### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

##### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

##### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

##### Safety

|                               |                         |
|-------------------------------|-------------------------|
| Protection class              | Isolation class I       |
| Impact resistance IK          | IK05                    |
| Ingress Protection (IP) class | IP30                    |
| Locking type                  | Barrel lock<br>Key lock |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |