




EEN003



Cell for twilight switch, wall mounted

Technical Features

Use conditions

Operating temperature	-10 - +45 °C
Air humidity protection	90%/20°C

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Mounting type	Surface mounting
---------------	------------------

Dimensions

Maximum connection distance between receiver and transmitter	100 m
--	-------

Cable

Cable length	1 m
--------------	-----

Dimensions

Height	118 mm
Width	48 mm

Power supply

Supply voltage	230 V +10%/-15%
----------------	-----------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Equipment

Type of probe	Light sensor
---------------	--------------

Detection

Type of sensor	Light sensor integrated
----------------	-------------------------

Settings

Switch off delay time	80 s
Switch on delay time	60 s

Connection

Conductor cross-section	0.2 - 1.5 mm ²
-------------------------	---------------------------

Lighting

Brightness measuring range	5 - 2000 lx
----------------------------	-------------

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------