



BF226

**Technical Features**

**Architecture**

Neutral position	Left
Number of poles	2

**Capacity**

Number of modules	2
-------------------	---

**Voltage**

Rated operational voltage $U_e$	230 - 400 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current $I_{dn}$	300 mA
Rated current	25 A

**Installation, mounting**

Nominal tightening torque	1.70 - 1.70 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

**Illustrations | Drawings**

