



WGMHDC

16AX DND&MUR SWITCH W/ LED (INDOOR)

Technical Features

Electric current

Switching current	16 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Untreated
-----------	-----------

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Dimensions	86 x 86 mm
------------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Electric current

Rated current	16 A
---------------	------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----