

Product Datasheet

HCB250Z

Switch X250 3P 250A	
Technical Features	
Electric current	
Rated current	250 A
Rated short-time withstand current I _{cs} IEC 60947	3 kA
Architecture	
Number of poles	3
Control/operation element	Toggle
Connection	
Cross-section rigid conductor	35 - 185 mm ²
Cross-section flexible conductor	35 - 150 mm ²
Voltage	
Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Frequency	
Frequency	50 - 60 Hz
Functions	
Trip unit	Switch
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes