



VD106TF

Small distributor, IC², surface, 1 row, 6 M, IP40, MS-terminal, N, transparent door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 6

Functions

With conduit inlets Yes

Dimensions

Height 170 mm

Width 134.50 mm

Depth 91 mm

Cover, door

Number of cabinet doors 1

Number of locks 0

Dimensions

Number of width units 6

Cover, door

Door/cover is transparent Yes

Materials

Material Polystyrene (PS)

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Locking type Snap on lock
Without lock

Glow wire test 650 °C

Sustainability

RoHS conform Yes