



VYGMQ12

Metering Enclosure, GME, QLD, fitting with 12pcs meters, IP23

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Breaking and opening capacity Idm	0 kA
-----------------------------------	------

Equipment

Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	No chassis

Capacity

Number of modules	56
-------------------	----

Dimensions

Height	1177 mm
Width	1140 mm
Depth	365 mm

Cover, door

Number of cabinet doors	2
Door/cover is transparent	No

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP23
Locking type	3-point lever Key lock

Architecture

Number of poles	56
-----------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes