



VYGMQ12

**Metering Enclosure, GME, QLD, fitting with 12pcs meters, IP23**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Breaking and opening capacity I <sub>dm</sub>	0 kA
---	------

**Equipment**

Has mounting plate	No
Equipped with switch	No switch
Number of switches	0
Type of busbar chassis	No chassis

**Capacity**

Number of modules	56
-------------------	----

**Dimensions**

Height	1177 mm
Width	1140 mm
Depth	365 mm

**Cover, door**

Number of cabinet doors	2
Door/cover is transparent	No

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP23
Locking type	3-point lever Key lock

**Architecture**

Number of poles	56
-----------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes