



WXF063

Touch dimmer Gallery

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Material	Polycarbonate (PC)

Dimensions

Height	45 mm
Width	45 mm

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Lighting

LED lamp power	70 W
----------------	------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Capacity

Number of modules	2
-------------------	---

Texts

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Installation mode	For catch fixing
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

Sustainability

RoHS conform	Yes
--------------	-----