



WXF063

**Touch dimmer Gallery**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour Grey

RAL code 7011

Material Polycarbonate (PC)

**Dimensions**

Height 45 mm

Width 45 mm

**Architecture**

Control/operation element Single push button

**Lighting**

LED lamp power 70 W

**Use conditions**

Operating temperature -10 - 35 °C

**Capacity**

Number of modules 2

**Texts**

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Installation mode For catch fixing

Type of connection With screw terminals

Operation and control No Bluetooth interface

**Sustainability**

RoHS conform Yes