



WXF062

Rotary dimmer Gallery eco lamps

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Material	Polycarbonate (PC) Thermoplastic

Dimensions

Height	45 mm
Width	45 mm

Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

Power

Power incandescent lamp	20 - 300 W
-------------------------	------------

Lighting

LED lamp power	70 W
----------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section rigid conductor	1.5 - 2.5 mm ²
Cross-section flexible conductor	1.5 mm ²

Capacity

Number of modules	2
-------------------	---

Texts

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Type of connection	With screw terminals
Operation and control	No Bluetooth interface

Sustainability

RoHS conform	Yes
--------------	-----