



WXF062

**Rotary dimmer Gallery eco lamps**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour Grey

RAL code 7011

Material Polycarbonate (PC)  
Thermoplastic

**Dimensions**

Height 45 mm

Width 45 mm

**Architecture**

Control/operation element Push & rotative switch

**Power**

Power incandescent lamp 20 - 300 W

**Lighting**

LED lamp power 70 W

**Use conditions**

Operating temperature -5 - 45 °C

**Connection**

Cross-section rigid conductor 1.5 - 2.5 mm<sup>2</sup>

Cross-section flexible conductor 1.5 mm<sup>2</sup>

**Capacity**

Number of modules 2

**Texts**

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Type of connection With screw terminals

Operation and control No Bluetooth interface

**Sustainability**

RoHS conform Yes