



JK066_IMG

66 Mod DIN Rail Box Plain

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	100 A
---------------	-------

Equipment

Number of rows	3
With lock	Yes
Has neutral terminal block	Yes

Capacity

Number of modules	66
-------------------	----

Dimensions

Height	708 mm
Width	505 mm
Depth	125 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	66
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Barrel lock Key lock

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes