



WNA682B

IP55

cubyko Double horizontal box empty with 2 sliders white IP55

Technical Features

Capacity

Number of modules	2
-------------------	---

Materials

Colour	Pure white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Number of units	1
Height	76 mm
Width	147 mm
Depth	56 mm

Equipment

With cable entry	Yes
------------------	-----

Installation, mounting

Mounting-/Connection Position	Horizontal
Mounting on	Surface mounting

Accessories

With frame cover	Yes
------------------	-----

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK07

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For horizontal mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Suitable for

cubyko	
cubyko	

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes