



VML_SIZE_5

14 Way 100A 30mA Type ARCCB Incomer

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
----------------------------	-----

Capacity

Number of modules	14
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	98.20 mm
Height	245 mm
Width	368.40 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

Colour	Pure white
Material	Steel

Connection

Number of accessible phases	2
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	2

Equipment

Number of rows	1
With socket outlet	No

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Sustainability

RoHS conform	Yes
--------------	-----