


Product Datasheet

WXF023



WXF023

Switch gallery InterBP 2 modules external signal

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Middle plate
----------------------	--------------

Connectivity

Mounting type	Click mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	45 x 45 mm
Built-in depth	34 mm
Built-in depth flush-mounted boxes	34 mm

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Texts

Lighting	Optional function display possible via status LEDs
Switch mode	1NO, 1NC, separate input terminals

Sustainability

REACH-SVHC free	Yes
-----------------	-----