



WXF024

**Push-button gallery 2 way push button 2 modules pull cord**

**Technical Features**

**Frequency**

Frequency 50 - 60 Hz

**Architecture**

Number of poles 2

**Materials**

Colour Grey

Surface finish Matt

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

**Dimensions**

Height 45 mm

Width 45 mm

Depth 40.35 mm

Built-in depth flush-mounted boxes 41 mm

**Controls and indicators**

Number of buttons 0

With feedback signal contact No

**Safety**

Ingress Protection (IP) class IP21

Impact resistance IK IK05

**Accessories**

Has labelling field No

**Use conditions**

Operating temperature -10 - 35 °C

**Texts**

Imprint Without imprint

Type of connection With Sanvis terminal

**Suitable for**

gallery

**Sustainability**

REACH-SVHC free Yes