



LF1001009016

Trunking made of PVC LF 10x10mm traffic white

Technical Features

Dimensions

Height	10 mm
Width	12 mm
Length	2000 mm
Inner cross-section	84 - 84 mm²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	0
--	---

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK06
Ingress Protection (IP) class	IP30

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Without coupling
-------------------	------------------

Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	No
With protective film	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

