




WRPS42BSB

10AX 4 Gang 2 Way Wall Switch Brushed Steel Black Insert

Technical Features

Electric current	
Switching current	10 A

Installation, mounting	
Mounting on	Flush mounting

Voltage	
Rated voltage	250 V

Materials	
Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

Identification	
Assembly arrangement	Basic element with full cover plate

Connectivity	
Mounting type	Screw mounting

Controls and indicators	
Number of buttons	4

Dimensions	
Dimensions	86 x 146 mm
Built-in depth	11.20 mm

Safety	
Ingress Protection (IP) class	IP20

Architecture	
Control/operation element	4-gang rocker

Electric current	
Rated current	10 A

Texts	
Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes