



10527004

Surface-mtd housing 2gang hor., K.5, stainless steel matt, lacq.

Technical Features

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Materials

| | |
|----------------|----------------------------------|
| Colour | Stainless steel |
| RAL code | 9022 |
| Surface finish | Matt |
| Material | Stainless steel Thermoplastic |
| Treatment | Untreated Varnished |

Dimensions

| | |
|----------------|-----------|
| Height | 82 mm |
| Width | 159.50 mm |
| Depth | 41.50 mm |
| Built-in depth | 36 mm |

Equipment

| | |
|------------------|-----|
| With cable entry | Yes |
|------------------|-----|

Installation, mounting

| | |
|-------------------------------|------------------|
| Mounting-/Connection Position | Horizontal |
| Mounting on | Surface mounting |

Accessories

| | |
|------------------|----|
| With frame cover | No |
|------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-------------------|---|
| Installation mode | For mounting on combustible base surface For horizontal mounting |
|-------------------|---|

Suitable for

| | |
|-----|--|
| K.x | |
| K.5 | |