

# Product Datasheet

## BF441



BF441

### Technical Features

#### Architecture

Neutral position	Left
Number of poles	4

#### Capacity

Number of modules	3
-------------------	---

#### Voltage

Rated operational voltage $U_e$	230 - 400 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Electric current

Rated residual operating current $I_{dn}$	300 mA
Rated current	40 A